
PA10MSO-OT-x Data Sheet 10 MSOP socket/10 pin DIP 0.3" or 0.6" plug

Supported Device/Footprints


Using this adapter, 10 pin MSOP packages with a body width of 3.0mm and a lead pitch of 0.5mm can be programmed on DIP programmers.

This adapter accepts devices of the following dimensions:



Body mm (inches)			Knee mm (inches)		
min.	typ.	max.	min.	typ.	max.
n/a	3.0	3.1	n/a	3.8	3.9
	(0.118)	(0.122)		(0.150)	(0.154)
Tip mm (inches)			Body	Length	Lead Pitch
min.	typ.	max.	n/a		0.5
4.8	4.9	n/a			(0.0197)
(0.189)	(0.193)				

Adapter Dimensions



Adapter Construction

The adapter is made up of 2 sub-assemblies. They assemble via connectors making the adapter modular. This way the sub-assemblies can be replaced when they wear out.

When disassembling the adapter take care not to bend the pins. When reassembling the adapter note the pin 1 indicators to align the parts correctly.

Test Socket

MSOP Open-top test socket: Wells Part #: 656-0102211

LSC Part #: 10SJ-656-W

10MSOP

Accepts the test socket and provides a DIP plug.

Wiring

Wiring is 1 to 1. Pin 1 of the MSOP device is wired to pin 1 of the DIP plug. Pin 2 to pin 2 and so on around the adapter.



PA10MSO-OT-x Data Sheet Doc: 10MSOP.DOC Rev 04/14/04 Page 1 of 1